

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301540073](#)
Status: **Active**
Overview: [Heavy-Duty Industrial Wiring Devices](#)
Description: Super-Safeway Standard Molded Y Cordset, 2 Pole/3 Wire SOOW Cordset, Cordset Length 0.91m (3.0'), NEMA L6-30, 250V

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Wiring Devices
Series	130154
IP Rating	N/A
NEMA Configuration	NEMA L6-30
Overview	Heavy-Duty Industrial Wiring Devices
Product Name	Super-Safeway
Receptacle Type	Duplex
Specialty	N/A
Taxonomy	Wiring Devices
Type	Molded Y Cordset
UPC	78678898165

Physical


Flange	No
Flip Lid	No
Gender	Male-Female
Length	0.91m (3.0')
Locking Blade	Yes
Poles	2-pole/3-wire

Electrical

Cord Type	12/3 SOOW
Current - Maximum per Contact	30.0A
GFCI	No
Lighted Connector	No
Voltage - Maximum	250V

Material Info

Engineering Number	2848-Y
--------------------	--------



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130154 Series](#)