

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301550148](#)
Status: **Active**
Overview: [Watertite Extreme Wet-Location Wiring Solutions](#)
Description: [Watertite Extreme Connector with California Style Locking Blade, 3 Pole/4 Wire, Non-NEMA, 480V, Cord Grip Body Size F5](#)

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E10176

General

Product Family [Wiring Devices](#)
 Series [130155](#)
 IP Rating IP67
 NEMA Configuration [Non-NEMA Locking CA](#)
 Overview [Watertite Extreme Wet-Location Wiring Solutions](#)
 Product Name [Watertite Extreme](#)
 Receptacle Type [Single](#)
 Specialty [N/A](#)
 Taxonomy [Wiring Devices](#)
 Type [Connector](#)
 UPC [78678801474](#)

Physical

Cord Grip Body Size [F5 1 1/4"](#)
 Flange [No](#)
 Flip Lid [No](#)
 Gender [Female](#)
 Length [N/A](#)
 Locking Blade [Yes](#)
 Net Weight [0.780/kg](#)
 Poles [3-pole/4-wire](#)

Electrical

Cord Type [N/A](#)
 Current - Maximum per Contact [50.0A](#)
 GFCI [No](#)
 Lighted Connector [No](#)
 Voltage - Maximum [480V](#)

Material Info

Engineering Number [CS81W64](#)



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130155 Series](#)