

GPI Product Details



GPI

(1423156-1)

TE Part Number: 1423156-1

✓ Active

[Add to Part List](#)

Control Relays

[Not EU RoHS or ELV Compliant](#)

Product Highlights:

- GP Series
- Power
- AC Actuating System
- Input Voltage = 120 VAC
- Contact Arrangement = 1 Form C, SPDT, 1 C/O

[View all Features](#) | [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Power
- Termination Type = 16 Flat Base Pins

Electrical Characteristics:

- Actuating System = AC
- Input Voltage (VAC) = 120
- Contact Rating = 10A Resistive @ 220 VAC/48 VDC

Body Related Features:

- [Series](#) = GP

Contact Related Features:

- Approved Standards = CSA Certified, UL Listed
- Approx. Dimensions (L x W x H) (mm [in]) = 45.00 x 45.00 x 109.00 [1.773 x 1.773 x 4.294]
- Mounting Options = Socket

Configuration Related Features:

- [Contact Arrangement](#) = 1 Form C, SPDT, 1 C/O

Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process

Conditions for Usage:

- Temperature Range (°C) = 0 – 60

Other:

- Brand = Agastat