

## 1534808-1 Product Details



**1534808-1**

TE Internal Number: 1534808-1

✓ [Active](#)

### Cable Clamps

✓ [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Backshell/Cable Clamp
- Cable Clamp Type = Single or Dual Cable Entry
- Ferrule Type = Crimp
- 45° Cable Exit Angle
- Cable Insulation Diameter = 4.83 - 6.10 mm, 5.84 - 7.11 mm, 7.62 - 8.89 mm, 9.65 - 10.92 mm

[View all Features](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#)

[Live Product Chat](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [HD20 - COVER KIT \(15 POS.\) HD20 - KAPPENKIT \(15 POL....](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- [HD20 Cover Kits with 2 cable outlets 45?](#) (PDF, German)

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Product Type](#) = Backshell/Cable Clamp
- Cable Clamp Type = Single or Dual Cable Entry
- Number of Positions = 15
- [Shell Size](#) = 2
- [Shielded](#) = Yes
- [Screws and Retainer Clips](#) = With
- [Grommets](#) = Without
- [Slide Latch](#) = Without
- Thread Size = 4-40

#### Electrical Characteristics:

- Screw Head Type = Phillips

#### Body Related Features:

- [Ferrule Type](#) = Crimp
- [Cable Exit Angle](#) = 45°
- [Cable Insulation Diameter \(mm \[in\]\)](#) = 4.83 - 6.10 [0.190 - 0.240], 5.84 - 7.11 [0.230 - 0.280], 7.62 - 8.89 [0.300 - 0.350], 9.65 - 10.92 [0.380 - 0.430]
- Cable Clamp Material = Die Cast
- Shield Plating = None

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Packaging Related Features:

- [Packaging Method](#) = Individual Kit

#### Other:

- Brand = AMP