

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1722583104](#)  
**Status:** **Active**  
**Overview:** Ultra-Fit Power Connectors  
**Description:** Ultra-Fit Tangless Receptacle Housing, 3.50mm Pitch, Dual Row, 4 Circuits, Black, Glow-Wire Capable

**Documents:**

<a href="#">3D Model</a>	<a href="#">Product Specification 1723231000-PS-SK-000 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">Product Specification PS-172323-0001-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Application Specification 1723230003-000 (PDF)</a>
<a href="#">Product Specification 1723230001-TS-000 (PDF)</a>	<a href="#">Packaging Specification 1723230004-000 (PDF)</a>
<a href="#">Product Specification 1723231000-PS-CH-000 (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Product Specification 1723231000-PS-ES-000 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification 1723231000-PS-JP-000 (PDF)</a>	

**General**

Product Family	Crimp Housings
Series	<a href="#">172258</a>
Application	Power, Wire-to-Board
Overview	<a href="#">Ultra-Fit Power Connectors</a>
Product Name	Ultra-Fit
Taxonomy	Connector Housings
UPC	191128803557

**Physical**

Circuits (maximum)	4
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1.464/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.50mm
Pitch - Termination Interface	3.50mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C

**Material Info**

**Reference - Drawing Numbers**

Application Specification	1723230003-000
Packaging Specification	1723230004-000
Product Specification	1723230001-TS-000, 1723231000-PS-CH-000, 1723231000-PS-ES-000, 1723231000-PS-JP-000, 1723231000-PS-SK-000, PS-172323-0001-001
Sales Drawing	1722580003-000



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2022)4187-DC (10  
June 2022)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[172258](#) Series

**Mates With**

Ultra-Fit Vertical Header [1722981104](#) ,  
[1722981204](#) , [1722981304](#) , [1722991104](#)  
 , [1722991204](#) , [1722991304](#) <br>Ultra-  
Fit Right-Angle Header [1723161104](#) ,  
[1723161204](#) , [1723161304](#)

**Use With**

Ultra-Fit Tangless Female Crimp  
Terminals:<br> [1722536011](#) (0.38µm  
Gold, 16-18 AWG)<br> [1722536111](#)  
(0.38µm Gold, 20-22 AWG)<br> [1722536012](#) (0.76µm Gold, 16-18  
AWG)<br> [1722536112](#) (0.76µm Gold,  
20-22 AWG)<br> [1722537023](#) (Tin,  
16-18 AWG)<br> [1722537123](#) (Tin, 20-22  
AWG)<br> Ultra-Fit Tangless Pre-Crimped  
Leads<br> [797582141](#) , [797582142](#)  
<br> Ultra-Fit Tangless TPA Retainer  
[1722644002](#)

This document was generated on 09/03/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**