


## 1 - 1520237 - 0 Product Details



**1 - 1520237 - 0**

[Active](#)

### Power Toggle Switches

[Not ELV or RoHS Compliant](#)

#### Product Highlights:

- ? Double Pole - Single Throw Configuration (Pole - Throw)
- ? Toggle Length = 17.07 mm
- ? Toggle Style = Baton
- ? Bushing Length = 11.91 mm
- ? Termination Type = Screw -In Terminal

[View all Features](#)

### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- ? [DIM'S FOR DBL. POLE TOOL HANDLE SW. FOR EUROPEAN USE](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- ? None Available

#### Product Specifications:

- ? None Available

#### Application Specifications:

- ? None Available

#### Instruction Sheets:

- ? None Available

#### CAD Files:

- ? None Available

#### Related Products:

- ? [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- ? Configuration (Pole - Throw) = Double Pole - Single Throw
- ? Termination Type = Screw -In Terminal

#### Electrical Characteristics:

- ? UL/CSA 125V Current Rating (Amps.) = 16
- ? UL/CSA 250V Current Rating (Amps.) = 8
- ? UL/CSA 125V Horse Power Rating (hp) = 1.00

#### Housing Related Features:

- ? Toggle Length (mm [in]) = 17.07 [0.672]
- ? Toggle Style = Baton

#### Configuration Related Features:

- ? Bushing Length (mm [in]) = 11.91 [0.469]

#### Industry Standards:

- ? [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process

#### Other:

- ? Brand = Alcoswitch