

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [120084-0028](#)
Status: **Active**
Overview: Brad® Ultra-Lock® Connection System
Description: Ultra-Lock® (M12) Receptacle, Female, 4 Poles, M16x1.5 Mounting Threads, PCB Pins, 5.00mm Stand-off

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Receptacles
Series	120084
IP Rating	IP69K
NEMA Rating	NEMA 6
Overview	Brad® Ultra-Lock® Connection System
Product Name	Ultra-Lock® (M12)
Type	PCB Mount
UPC	78678812015

Physical

Coupling Type	External Thread
Gender	Male
Keyway	Single
Length	N/A
Material - Component	Nickel-plated Brass
Mounting Thread Size	M16 x 1.5
Net Weight	15.040/g
Orientation	Straight
Panel Mount	Back
Poles	4
Temperature Range - Operating	-25°C to +90°C
Wire Size AWG	N/A
Wire/Cable Type	N/A

Electrical

Current - Maximum per Contact	4A
Voltage - Maximum	250V AC/DC

Material Info

Old Part Number	WR4U46000
-----------------	-----------

Reference - Drawing Numbers

Sales Drawing	SD-120084-007
---------------	---------------



image - Reference only

EU RoHS

RoHS Compliant by Exemption

REACH SVHC

Not Reviewed

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[120084Series](#)