

[My Cart](#)[My Part Lists](#)[Sign In/Register](#)[English \(Change\)](#)**Have a Question?**

Chat with a Product Information Specialist

[Products](#)[Industries](#)[Resources](#)[About TE](#)[Support Center](#)[My Account](#)[Home](#) > [Products](#) > [Switches & Knobs](#) > [Product Feature Selector](#) > Product Details[Share](#)[Print](#)[Email](#)

## 2-1825138-5 Product Details

**2-1825138-5**

TE Internal Number: 2-1825138-5

**Active**

### Toggle Switches

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- A Series
- Double Pole - Double Throw Configuration (Pole-Throw)
- Current Rating = 5 A
- Mount Style = Through-Hole
- Termination Type = Printed Circuit

[View all Features](#)[Add to My Part List](#)[Request Sample](#)[Find Similar Products](#)[Buy Product](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [GEMINI A SERIES TOGGLE SWITCH, DOUBLE POLE, 2 POSITI...](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- [SWITCHES\\_CORE\\_PROGRAM\\_CATALOG](#) (PDF, English)
- [GEMINI SERIES SWITCHES QUICK REF GUIDE 2-1773458-5](#) (PDF, English)

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Additional Product Images:

- [Product Photo](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Configuration (Pole-Throw) = Double Pole - Double Throw
- Termination Type = Printed Circuit

#### Electrical Characteristics:

- Current Rating (A) = 5

#### Termination Related Features:

- Seal Type = Terminal Seal (epoxy)

#### Body Related Features:

- Series = A
- Mount Style = Through-Hole

#### Contact Related Features:

- Contact Plating = Silver

#### Housing Related Features:

- Toggle Actuation = Vertical
- Toggle Style = Baton Long
- Toggle Length (mm [in]) = 10.40 [0.410]
- Process Sealed = No
- Bushing Style = Threaded
- Bushing Type = 1/4-40

#### Configuration Related Features:

- [Operating Function](#) = On On

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Other:

- Brand = Alcoswitch

### Corporate Information

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

### Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

### Customer Support

- [Email or Chat with Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage Your Account](#)

### Sign up for our eNewsletter

 

### Follow Us On:



### Visit Us On:

