

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300960046](#)  
**Status:** **Active**  
**Overview:** Strain-Relief Cord Grips  
**Description:** Liquid-Tight Grip Strain Relief, 1" NPT, 45° Angle Male, Mesh Length 0.133m (5.25")

**Documents:**

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)  
[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR32159  
 UL E61303

**General**

Product Family Cable Grips  
 Series [130096](#)  
 Eye Type N/A  
 NEMA Rating NEMA 4  
 O-Ring N/A  
 Overview [Strain-Relief Cord Grips](#)  
 Product Literature Order No 987651-6081  
 Product Name Liquid-Tight  
 Type Strain Relief Grip  
 UPC 78678836392  
 Use With MAX-LOC Lock Nut 1" NPT [130099-0145](#) , MAX-LOC Gasket Sealing Ring 1" NPT [130099-0151](#) , MAX-LOC O-Ring, 1" NPT [130180-0334](#)  
 Woodhead Yes

**Physical**

Approximate Break Strength N/A  
 Bale Length N/A  
 Body Style 45° Angle  
 Cable Diameter N/A  
 Color - Grommet N/A  
 Gender Male  
 Material - Body Malleable Iron, Zinc Plated Steel  
 Material - Grip Stainless Steel  
 Mesh Length 0.133m (5.25")  
 Number of Holes N/A  
 Thread Size 1" NPT

**Material Info**

Engineering Number 36392

**Reference - Drawing Numbers**

Sales Drawing SD-130096-102



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS Not Reviewed  
 ELV Not Reviewed  
 RoHS Phthalates Not Reviewed

**Search Parts in this Series**

[130096 Series](#)