

## 3-1825910-1 Product Details

 [Live Product Chat](#)


**3-1825910-1**

TE Internal Number: 3-1825910-1

 [Active](#)

### Pushbutton Switches

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Switch - Mechanical
- Tactile
- Single Pole - Single Throw Configuration (Pole-Throw)
- Contact Rating = 50mA
- Operating Function = Off [On]

[View all Features](#)

#### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

 [Add to My Part List](#)
 [Request Sample](#)
 [Find Similar Products](#)
 [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [6MM TACT SWITCH, THRU-HOLE HIGH TEMP \(PDF, English\)](#)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Product Type = Switch - Mechanical
- Tactile = Yes
- Configuration (Pole-Throw) = Single Pole - Single Throw
- Mount Angle = Vertical
- Termination Type = Printed Circuit
- Actuator Style = Round
- Comment = (On) indicates momentary position.

#### Electrical Characteristics:

- Contact Rating = 50mA

#### Body Related Features:

- [Series](#) = FSM
- Mount Style = Through-Hole
- Actuator Length (mm [in]) = 13.40 [0.527]
- Actuator Profile = Extended
- Actuator Color = Black
- Case Material = Nylon
- Actuator Material = Nylon

#### Contact Related Features:

- Contact Plating = Silver

#### Housing Related Features:

- Process Sealed = No
- Low Profile = No

#### Configuration Related Features:

- Operating Function = Off [On]
- Ganged = No
- ESD Grounding Terminal = Without
- Actuator Force (g [oz]) = 160.00 [5.648]
- Number of Actuators = Single
- Illuminated = No
- Dust Proof = No
- Support Bracket = Without
- Snap Action = Without

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Conditions for Usage:

- Temperature Rating = High

#### Packaging Related Features:

- Packaging Method = Loose Piece

#### Other:

- Brand = Alcoswitch

 [BOOKMARK](#) 

#### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

#### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

#### Customer Support

[Email or Chat with Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage Your Account](#)