


## 42634 -3 Product Details

**Live Product Chat** US Only  
8:30am - 5pm ET, Mon - Fri



**42634 -3**

[Active](#)

### Taper Pins and Blocks

[Not reviewed for RoHS Compliance](#)

#### Product Highlights:

- ? Taper Pins
- ? Pin Type = Solid
- ? Pin Style = Long Shoulder
- ? 53 Series
- ? Loose Piece

[View all Features](#) | [Find Similar Products](#)

### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling Product Feature Selector](#)
- [Contact Us About This Product](#)

### Documentation & Additional Information

#### Product Drawings:

- ? [TAPER PIN ASSY, "53" SERIES P.I.D.G.](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- ? None Available

#### Product Specifications:

- ? [Contact, TAYP -AIR Pins and Blocks](#) (PDF, English)
- ? [Contact, Taper Pins](#) (PDF, English)

#### Application Specifications:

- ? None Available

#### Instruction Sheets:

- ? None Available

#### CAD Files:

- ? None Available

#### Additional Information:

- ? [Product Line Information](#)

#### Related Products:

- ? [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- ? Product Type = Taper Pins
- ? Insulation Support = Pre -Insulated
- ? Insulation Diameter (mm [in]) = 1.52 - 2.54 [0.060 - 0.100]
- ? Finish = Gold (30)
- ? Comment = For Stranded Wire Only.

#### Body Related Features:

- ? Pin Type = Solid
- ? Pin Style = Long Shoulder
- ? Series = 53
- ? Wire Range (mm [AWG]) = 0.50 -0.90<sup>2</sup> [20-18]
- ? Insulation Color = Natural
- ? Overall Length (mm [in]) = 21.59 [0.850]
- ? Mates With = 53 Series Connector Block

#### Industry Standards:

- ? [RoHS/ELV Compliance](#) = Not reviewed for ELV/RoHS compliance
- ? [Lead Free Solder Processes](#) = Not reviewed for lead free solder process

#### Packaging Related Features:

- ? Packaging Method = Loose Piece

#### Other:

- ? Brand = AMP