


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [5044490607](#)
Status: **Active**
Overview: Pico-Clasp Wire-to-Board Connectors
Description: 1.00mm Pitch Pico-Clasp Wire-to-Board Header, Surface Mount, Single Row, Vertical, 0.10µm Gold Plated, with Inner Positive Lock, with Pick-and-Place Tape, 6 Circuits

Documents:

3D Model	Application Specification 5013300000-A01 (PDF)
Drawing (PDF)	Packaging Specification SPK-504449-001-001 (PDF)
Product Specification PS-504449-001-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification 5013300000-A00 (PDF)	



General

Product Family	PCB Headers
Series	504449
Application	Signal, Wire-to-Board
Overview	Pico-Clasp Wire-to-Board Connectors
Product Name	Pico-Clasp
UPC	887191268170

Physical

Breakaway	No
Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Polyamide
Net Weight	147.800/mg
Number of Rows	1
Orientation	Vertical
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.00mm
Plating min - Mating	0.102µm
Plating min - Termination	0.102µm
Polarized to Mating Part	Yes
Polarized to PCB	No
Robotic Placement	Vacuum Pick-Up Tape
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-40° to +85°C
Termination Interface: Style	Surface Mount

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	50V AC (RMS)/DC

Material Info

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[504449 Series](#)

Mates With

[Pico-Clasp Female Housing 501330](#)

Reference - Drawing Numbers

Application Specification

5013300000-A00, 5013300000-A01

Packaging Specification

SPK-504449-001-001

Product Specification

PS-504449-001-001

Sales Drawing

SD-504449-002, SD-504449-004

This document was generated on 02/14/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION