

K45C334 Product Details



High Voltage Relays

[Not EU RoHS or ELV Compliant](#)

Product Highlights:

- Contact Arrangement = 1 Form A, SPST-NO, 1 N/O, 1 Form B, SPST-NC, 1 N/C, 1 Form C, SPDT, 1 C/O
- Power Switching = Make Only, Yes, No
- Contact Current Rating = 0 - 15 Amps.
- RF Rated
- Coil Voltage = 26.5 VDC

[View all Features](#) | [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

K45C334

(5-1618240-7)

TE Part Number: 5-1618240-7

✓ [Active](#)

[Add to Part List](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Termination Style](#) = Bus Wire

Electrical Characteristics:

- [Contact Current Rating \(Amps.\)](#) = 0 - 15
- [RF Rated](#) = Yes
- [Coil Voltage \(VDC\)](#) = 26.5
- [Voltage, Max. \(VDC\)](#) = 0 - 5000
- Current, Carry Only = Yes

Termination Related Features:

- [High Voltage Connection \(Power\)](#) = High Voltage Tab
- [High Voltage Connection \(Coil\)](#) = Bus Wire
- [Auxiliary Contacts](#) = Without

Body Related Features:

- [Mount Style](#) = Non-Flanged

Configuration Related Features:

- [Contact Arrangement](#) = 1 Form A, SPST-NO, 1 N/O, 1 Form B, SPST-NC, 1 N/C, 1 Form C, SPDT, 1 C/O
- [Power Switching](#) = Make Only, Yes, No
- [Economizer](#) = Without

Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not suitable for lead free processing

Other:

- Brand = Kilovac