

Search for:

Products & Services

Company Name



www.ebmpapst.us

QLZ06AC Series Crossflow Blower



Specifications

Stock #	▶ 55412.70305
Model	▶ QLZ060030A583030LH133ACW
Air Flow Rate @ 0 PSI (CFM)	▶ 138
Impeller Size (mm)	▶ na
Curve	▶ 3
Voltage Range, Fans (V)	▶ na
Voltage (V)	▶ 115
Frequency (Hz)	▶ 50
Power Consumption (W)	▶ 56
Noise (dBA)	▶ 50
Ambient Temperature, Maximum (C.)	▶ 60

Bearing - Motor, Fan, Compressor	▶ Sleeve
Bobbin Position	▶ Front
Capacitance - Fan (mfd)	▶ na
Insulation Class	▶ H
Motor Orientation	▶ Left
Connector - Fitting (Fan)	▶ Terminals
Fan Size (mm)	▶ 60x300

[Click here for related products and specifications](#)

Component Database - Search 26,314 Global Manufacturers
[products & services](#) | [searchable catalogs](#) | [donations](#)
Database Last Updated: 01/01/06