

7-1618387-1 Product Details



7-1618387-1

TE Part Number: 7-1618387-1

✓ Active

➤ [Add to Part List](#)

Contactors

🌿 [Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- Contactor Type = Sealed
- LEV200 Series
- DC Actuating System
- Number of Poles = 1
- Contact Arrangement = 1 Form X, SPST-NO-DM

[View all Features](#) | [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Contactor Type = Sealed
- Terminal Type = 10-32 Stud

Electrical Characteristics:

- [Actuating System](#) = DC
- Contact Rating = 500A
- [Coil Voltage \(VDC\)](#) = 24
- [Coil Voltage, Max. \(VDC\)](#) = 24

Termination Related Features:

- Coil Termination = Wire

Body Related Features:

- Series = LEV200
- Torque = 80-100 in-lbs
- Mount Type = Bottom Mount

Contact Related Features:

- [Number of Poles](#) = 1

Configuration Related Features:

- [Contact Arrangement](#) = 1 Form X, SPST-NO-DM
- Auxiliary Switch Contact Arrangement = None
- Coil Wire Length (mm [in]) = 390 [15.3]

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Related Features:

- Packaging Method = Individual

Other:

- Brand = Kilovac