


8-34067-1 Product Details



8-34067-1

 [Active](#)

Splices - Closed Barrel

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Splice
- Not Sealed
- Splice Type = Butt
- Butt Splice Type = Standard
- Body Style = PLASTI-GRIP

[View all Features](#)

Quick Links

[Check Pricing & Availability](#)
[Search for Tooling](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [WIRE SPLICE PLASTI GRIP, BUTT, WIRE SIZE: 22 16](#) (PDF, English)

Catalog Pages/Data Sheets:

- [STANDARD TERMINALS AND SPLICES](#) (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- [PLASTI-GRIP Terminals and Splices](#) (PDF, English)

Instruction Sheets:

- [Pressure Type Wire Connector Chart PLASTI-GRIP Spli...](#) (PDF, English)

CAD Files: ([CAD Format & Compression Information](#))

- [3D Model](#) (STEP, Version G)
- [3D Model](#) (IGES, Version G)
- [2D Drawing](#) (DXF, Version G)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Splice
- [Sealed](#) = No
- [Splice Type](#) = Butt
- [Body Style](#) = PLASTI-GRIP
- [Insulation](#) = Yes
- [Insulation Support](#) = Insulation Support
- [Insulation Diameter \(mm \[in\]\)](#) = 3.05 [.120] Max.
- [Material](#) = Copper
- [Finish](#) = Tin
- Color = Red
- Comment = 22-16 splices are 22-18 range in accordance with MIL-T-7928.

Body Related Features:

- [Butt Splice Type](#) = Standard
- [Wire Range \(mm \[AWG\]\)](#) = 0.30-1.40² [22-16]
- [Wire Range \(CMA\)](#) = 509 – 3,260
- Insulation Sleeve Material = Vinyl

Industry Standards:

- Government/Industry Qualification = No
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Related Features:

- [Packaging Method](#) = Loose Piece
- Packaging Quantity = 100/Box

Other:

- Brand = AMP