


DOMINO D MODULE

Contact Plating: Silver xxx-xx-xxx07 Crimp Contacts: Insertable/Removable
 Gold xxx-xx-xxx09 Solder Contacts: Insertable/**Non-Removable**
 PCB Tail Contacts: Insertable/**Non-Removable**

Note: **These contacts are identical to those in the E module**


Performance data for D module: Pages 22, 24
 Ordering information: Page 27
 Crimp tooling information: Page 21
 Exploded view of module and contacts: Page 20



PIN HOUSING

765-13-0080D (without contacts)

Pin Contact Size 16	Contact Part N°	Dimensions	"A"		"B"		"C" Ø		"D" Ø	
			in	mm	in	mm	in	mm	in	mm
Crimp, Standard	701-13-02107		.33	8.38	n/a	n/a	.067	1.70	.062	1.57
Crimp, Premate	701-23-02107		.48	12.19	n/a	n/a	.067	1.70	.062	1.57
Crimp, Postmate	701-46-02107		.29	7.36	n/a	n/a	.067	1.70	.062	1.57
Solder, Standard	707-07-02107		.33	8.38	.19	4.82	.082	2.08	.062	1.57
Solder, Premate	707-13-02107		.48	12.19	.19	4.82	.082	2.08	.062	1.57
Solder, Postmate	707-41-02107		.29	7.36	.19	4.82	.082	2.08	.062	1.57
PCB Tail, Standard	707-34-02107		.33	8.38	.18	4.57	.062	1.57	.062	1.57
PCB Tail, Premate	707-42-02107		.48	12.19	.18	4.57	.062	1.57	.062	1.57
PCB Tail, Postmate	707-43-02107		.29	7.36	.18	4.57	.062	1.57	.062	1.57



SOCKET HOUSING

765-18-0080D (without contacts)

Socket Contact Size 16	Contact Part N°	Dimensions	"A"		"B"	
			in	mm	in	mm
Crimp	702-33-01107		n/a	n/a	.067	1.70
Solder	708-12-01107		.20	5.08	.082	2.08
PCB Tail	708-70-01107		.18	4.57	.062	1.57