

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1211290010](#)
Status: **Active**
Overview: mPm DIN Valve Connectors
Description: mPm DIN Screw M3 Steel-Zinc Plated, 27.00mm Length, 1 Bag of 100

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification PK-121129-001-001 \(PDF\)](#)

General

Product Family	Field Attachable / Accessories
Series	121129
IP Rating	IP65, IP67
Material - Contact	N/A
Overview	mPm DIN Valve Connectors
Product Name	mPm
Type	Field Attachable Connector
UPC	883906322175

Physical

Cable Diameter	N/A
Coupling Type	N/A
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	N/A
Keyway	None
Material - Connector Body	N/A
Material - Coupling Nut	N/A
Material - Plating Mating	n/a
Net Weight	146.000/g
Orientation	N/A
Pitch - Mating Interface	N/A
Poles	N/A
Temperature Range - Operating	N/A
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	N/A
Voltage - Maximum	N/A

Material Info

Engineering Number	3000-10_BAG
--------------------	-------------

Reference - Drawing Numbers

Packaging Specification	PK-121129-001-001
Sales Drawing	SD-121129-010

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[121129](#) Series