

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1200668084](#)  
**Status:** **Active**  
**Overview:**  
**Description:** Micro-Change (M12) Double-Ended Cordset, 5 Poles, Female (Straight) to Male (Straight), 0.34mm<sup>2</sup> PUR/PVC Cable, 1.0m (3.28') Length

**General**

Product Family	Industrial Cordsets
Series	<a href="#">120066</a>
Connector End A	Micro-Change (M12)
Connector End B	Micro-Change (M12)
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	microchange_m12_connectors
Product Name	Micro-Change (M12)
Region	Europe
Type	Double Ended
UPC	883906365295

**Physical**

Cable Diameter	5.70mm (.224")
Cable Length	1.0m (3.28')
Color - Cable Jacket	Black
Coupling Style	Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	No
Material - Cable Jacket	PUR/PVC
Material - Connector Body	PUR
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	30.445/g
Orientation	Straight to Straight
Poles	5
Temperature Range - Operating	-25°C to +80°C
Wire Size AWG	N/A
Wire/Cable Type	EU Cable

**Electrical**

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

**Material Info**

Engineering Number	885030P03M010
--------------------	---------------

**Reference - Drawing Numbers**

Sales Drawing	1200668084-000, SD-120066-029
---------------	-------------------------------

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Contained Per -  
D(2020)4578-DC (25  
June 2020)  
Lead

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[120066](#) Series