

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1729531801](#)  
**Status:** **Active**  
**Overview:** [Micro-Fit Connector System](#)  
**Description:** Micro-Fit Terminal Position Assurance (TPA) Retainer, 18 Circuits, 3.00mm Pitch, UL 94V-0, Low-Halogen, Natural

**Documents:**

<a href="#">3D Model</a>	<a href="#">Test Summary TS-43045-001-001 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">Test Summary TS-43045-002-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Product Specification PS-43045-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Packaging Specification 1729530001-PK-000 (PDF)</a>	

**General**

Product Family	Accessories
Series	<a href="#">172953</a>
Comments	See Product Specification for maximum current rating by circuit size and wire AWG
Component Type	Terminal Position Assurance
Overview	<a href="#">Micro-Fit Connector System</a>
Product Name	Micro-Fit TPA
UPC	889056430166

**Physical**

Circuits (Loaded)	18
Circuits (maximum)	18
Color - Resin	Natural
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.202/g
Number of Rows	1
Packaging Type	Bag
Temperature Range - Operating	-40° to +105°C

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	1729530001-PK-000
Product Specification	PS-43045-001
Sales Drawing	SD-172953-001-001
Test Summary	TS-43045-001-001, TS-43045-002-001



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)4578-DC (25  
June 2020)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[172953 Series](#)

**Use With**

Micro-Fit TPA Receptacle Housing Low-Halogen [172952](#) <br> Micro-Fit TPA Plug Housing [203632](#)