

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300840123](#)  
**Status:** **Active**  
**Overview:** Reels - Woodhead  
**Description:** Woodhead POW-R-MITE Heavy Duty Cable Reel with Retraction Weight of 4lbs., 14/12 SOW, 6.10m (20.0') Cord Length with Flying Leads

**Documents:**

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR29921

**General**

|                    |  |
|--------------------|--|
| Product Family     | Electric Reels   |
| Series             | <a href="#">130084</a>   |
| Cable Length       | N/A  |
| Comments           | Applications: Vertical Lift, Drag, Recovery and Horizontal Stretch with 10% Sag. |
| Depth              | 0.48m (19.00")   |
| Duty               | Heavy  |
| Enclosure Rating   | NEMA 3   |
| Height             | 0.52m (20.50")   |
| NEMA Configuration | N/A  |
| Overview           | <a href="#">Reels - Woodhead</a>   |
| Product Name       | POW-R-MITE   |
| Type               | Cable Reel   |
| UPC                | 78678827467  |
| Width              | 478.54mm (18.840")   |

**Physical**

|                          |                |
|--------------------------|----------------|
| Cable Movement           | Ratchet Lock   |
| Cord Length              | 6.10m (20.0')  |
| Drum Lock                | Ratchet        |
| Guide Arm                | 4 - Postion    |
| Material - Coating       | Powder Coating |
| Material - Housing       | Steel          |
| Mounting Style           | Rigid          |
| Number of Conductors     | 12             |
| Packaging Type           | Carton         |
| Primary Cord/Cable Entry | 1" NPT         |
| Retraction Weight        | 1.8kg (4.0 lb) |
| Wire Size AWG            | 14             |

**Electrical**

|                               |           |
|-------------------------------|-----------|
| Bulb Included                 | N/A       |
| Cord Type                     | 14/12 SOW |
| Current - Maximum per Contact | 7.0A      |
| GFCI                          | No        |
| Lamp Type                     | N/A       |
| Lamp Wattage - Maximum        | N/A       |
| On/Off Switch                 | N/A       |
| Voltage - Maximum             | 600V      |

**Material Info**

Engineering Number 92512AN



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130084 Series](#)

This document was generated on 07/27/2020

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**