

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300830782](#)  
**Status:** **Active**  
**Overview:** Reels - Woodhead  
**Description:** Woodhead POW-R-MITE Industrial Duty Cable Reel, 12/3 SOW, 15.24m (50.0') Cord Length with 15A Connector and Ball Stop

**Documents:**

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR29921

**General**

Product Family	Electric Reels
Series	<a href="#">130083</a>
Cable Length	N/A
Comments	Applications: Vertical Lift, Drag, Recovery and Horizontal Stretch with 10% Sag.
Depth	0.34m (13.50")
Duty	Industrial
Enclosure Rating	NEMA 4
Height	0.37m (14.50")
NEMA Configuration	NEMA 5-15
Overview	<a href="#">Reels - Woodhead</a>
Product Name	POW-R-MITE
Type	Cable Reel
UPC	78678835109
Width	244.35mm (9.620")

**Physical**

Cable Movement	Ratchet Lock
Cord Length	15.24m (50.0')
Drum Lock	Ratchet
Guide Arm	5° increments over 270° Arc
Material - Coating	Powder Coating
Material - Housing	Cast Aluminum
Mounting Style	Rigid
Number of Conductors	3
Number of Receptacles	1
Packaging Type	Carton
Primary Cord/Cable Entry	1" NPT
Retraction Weight	1.8kg (4.0 lb)
Wire Size AWG	12

**Electrical**

Bulb Included	N/A
Cord Type	12/3 SOW
Current - Maximum per Contact	18.0A
GFCI	No
Lamp Type	N/A
Lamp Wattage - Maximum	N/A
On/Off Switch	N/A
Voltage - Maximum	120V

**Material Info**

Engineering Number 92433-1547



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130083 Series](#)

This document was generated on 07/20/2020

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**