

Home: >

Part Number: 130008-0242

MC 12P MP 30' #16AWG STOOW

Image not available

Status: Active
Series: [130008](#)
Category: Molex Parts
Old Part Number: 302002A01F300

[CHECK DISTRIBUTOR INVENTORY](#)

[Add to MyParts](#)

Go to [Part Detail](#)

Series image - Reference only

Specifications & Other Documents:

Documents not available online

Note - Please disable browser pop-up blockers to view documents on www.molex.com

Product Environmental Compliance

Questions on Product Environmental Compliance? Email productcompliance@molex.com

EU RoHS: ELV and RoHS Compliant

China RoHS:

REACH SVHC: Not Reviewed

Low-Halogen Status: Not Reviewed

[Product Compliance Statement](#)

Application Tooling

[FAQ](#)

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)

Part Detail

[COLLAPSE ALL](#)

General

Status	Active
Category	Molex Parts
Series	130008
UPC	78678833934

Physical

Net Weight	568.800/g
------------	-----------

Agency Certification

Please find UL Certificates by searching the UL Database using the Molex Series Number. [Click here to visit the UL Database](#)

CSA	LR6837
UL	E152210

Material Info

Old Part Number	302002A01F300
-----------------	---------------

Molex Connectors

Wire-to-Board
Board-to-Board
Wire-to-Wire
Input/Output (IO)
FFC/FPC
Sockets

Other Products

Fiber Optic Products
Antennas
Industrial Automation
Membrane Switches
Copper Flex
PCB Assemblies
Woodhead Electrical
Solid State Lighting

Resources

Contact Us
Catalog
Cross-Reference
Industries
Literature
Product Name

Company Info

About Us
Careers
ecocare
Investors
Press Room
Shows & Events
Supplier Portal

Other Info

Feedback
Help
Legal Disclaimer
View Mobile Site
Privacy Policy
Sitemap

Stay Connected with Molex:

