

## 1-747579-1 Product Details

### Have a Question?

Chat with a Product Information Specialist



**1-747579-1**

TE Internal Number: 1-747579-1



Search for Replacement Parts

### Standard Cable Connectors

[Not EU RoHS or ELV Compliant](#) ([Find RoHS Compliant Alternates](#))

#### Product Highlights:

- Accessory
- Accessory Type = Ferrule
- Product Series = HDE-20 (IDC), HDP-20 (Crimp Snap), HDP-22 (Crimp Snap)
- Ferrule Shape = Stepped
- Shell Size = 1, 2, 3

[View all Features](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)
[Request Sample](#)
[Find Similar Products](#)
[Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [FERRULE, OUTER, SIZES 1 THRU 3, SHIELDING HARDWARE, ...](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- [AMPLIMITE SUBMINATURE D TYPE CONNECTORS](#) (PDF, English)
- [PERSONAL SYSTEMS PRODUCTS](#) (PDF, English)

#### Product Specifications:

- [Connector, AMPLIMITE, Shielding Hardware](#) (PDF, English)

#### Application Specifications:

- [AMPLIMITE HDE-20 Shielding Hardware Kits With and Wi...](#) (PDF, English)
- [AMPLIMITE Connectors for Coaxial and Signal HD-20 Co...](#) (PDF, English)

#### Instruction Sheets:

- [Shielding Hardware Kits w/AMPLIMITE hde-20 hdp-20 an...](#) (PDF, English)
- [Shielding Hardware Enclosure Kits with AMPLIMITE\\* HD...](#) (PDF, English)
- [Shielding Hardware Kits with AMPLIMITE HD-20 Solder ...](#) (PDF, English)
- [Crimping Die Assemblies f/AMPLIMITE Connectors](#) (PDF, English)

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Product Type](#) = Accessory
- [Accessory Type](#) = Ferrule
- [Product Series](#) = HDE-20 (IDC), HDP-20 (Crimp Snap), HDP-22 (Crimp Snap)
- [Shell Size](#) = 1, 2, 3
- [Shell Type](#) = Full Metal Shell
- [Grade](#) = Standard

#### Body Related Features:

- [Ferrule Shape](#) = Stepped
- [Cable Insulation Diameter \(mm \[in\]\)](#) = 8.23 - 9.53 [0.324 - 0.375]
- [Ferrule Material](#) = Steel (annealed)
- [Ferrule Plating](#) = Bright Tin-Lead

#### Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process

#### Other:

- [Brand](#) = AMP

BOOKMARK

### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

### Customer Support

[Email or Chat with Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage Your Account](#)

### Sign up for our eNewsletter

Enter your email address

### Follow Us On:

