




TXR40AC00-2206AI Product Details

[Share](#) | [Print](#) | [Email](#)


Braid, Fixed, Spin and Tinel Lock Adapters

TXR40AC00-2206AI

TXR40AC00-2206AI

TE Internal Number: 760950-000

Active

[View 3D PDF](#)

Product Highlights [View All](#)

- Applies To Cable
- Military Style Number = MIL-C-38999
- Style = Tinel Lock
- Connector Code = 40
- Straight

[Pricing & Availability](#)

[Request Sample](#)

[Add to My Part List](#)

[Buy Product through Distributor](#)

Feedback

[Documents](#) | [Features](#) | [Compliance](#)

Please Note:

Use the Product Drawing for all design activity

Product Type Features		Configuration Features	
Style ?	Tinel Lock	Braid ?	Single 36 AWG Braid
Angle ?	Straight	Industry Standards	
Connector Shell Size	22	Government/Industry Qualification	No
Finish	Electroless Nickel	Military Style Number	MIL-C-38999
Color	Bright	RoHS/ELV Compliance ?	RoHS compliant, ELV compliant
Dimensions		Lead Free Solder Processes ?	Not relevant for lead free process
Boot Diameter (mm [in]) ?	17.14 [0.675]	RoHS/ELV Compliance History	Always was RoHS compliant
Cable Diameter Range (mm [in])	4.50 - 8.70 [0.180 - 0.340]	Conditions for Usage	
Body Features		Applies To	Cable
Connector Code ?	40	Other	
Entry Size	6	Brand	Raychem
Material	Aluminum Alloy	Comment	For specific shell size information, refer to "Hardware" or Catalog.

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

