

Home: >

**Part Number: 130031-0040**

Image not available

**Status:** Active - Custom  
**Series:** [130031](#)  
**Category:** Molex Parts  
**Old Part Number:** DND5100-M005

[CHECK DISTRIBUTOR INVENTORY](#)

[Add to My Parts](#)

Go to [Part Detail](#)

Series image - Reference only

**Product Environmental Compliance**

Questions on Product Environmental Compliance? Email [productcompliance@molex.com](mailto:productcompliance@molex.com)

**EU RoHS:**RoHS Compliant by Exemption

**China RoHS:**

**REACH SVHC:**Not Reviewed

**Low-Halogen Status:**Not Reviewed

[Product Compliance Statement](#)

**Application Tooling**

[FAQ](#)

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

**Previously Available Application Tooling**

[Check our list of old tooling that used to be available for this part](#)

**Part Detail**

[COLLAPSE ALL](#)

▼ **General**

Status	Active - Custom
Category	Molex Parts
Series	<a href="#">130031</a>
UPC	78678898403

▼ **Agency Certification**

Please find UL Certificates by searching the UL Database using the Molex Series Number. [Click here to visit the UL Database](#)

CSA	LR6837
-----	--------

▼ **Material Info**

Old Part Number	DND5100-M005
-----------------	--------------

**Molex Connectors**

Wire-to-Board  
 Board-to-Board  
 Wire-to-Wire  
 Input/Output (IO)  
 FFC/FPC  
 Sockets

**Other Products**

Fiber Optic Products  
 Antennas  
 Industrial Automation  
 Membrane Switches  
 Copper Flex  
 PCB Assemblies  
 Woodhead Electrical  
 Solid State Lighting  
 Application Tooling

**Resources**

Contact Us  
 Catalog  
 Cross-Reference  
 Industries  
 Literature  
 Product Name

**Company Info**

About Us  
 Careers  
 ecocare  
 Investors  
 Press Room  
 Shows & Events  
 Supplier Portal

**Other Info**

Feedback  
 Help  
 Legal Disclaimer  
 Trademarks  
 View Mobile Site  
 Privacy Policy  
 Sitemap

**Stay Connected with Molex:**

