

Search:

- Connectors**
- Sockets / Edgecards**
- Cable Assemblies**
- Antennas**
- Fiber Optic Products**
- Printed Circuit Products**
- Automation / Industrial**
- Lighting Products**

Home:

Part Number: 130050-0098

ENET MMJ IND/RJ45 10T 5M



Status: Active
Series: [130050](#)
Category: Molex Parts
Old Part Number: ENP1135M050

[Add to My Parts](#)

Go to [Part Detail](#)

Specifications & Other Documents:

Documents not available online

Note - Please disable browser pop-up blockers to view documents on www.molex.com

Questions on Product Environmental Compliance? Email productcompliance@molex.com

EU RoHS: ELV and RoHS Compliant
China RoHS:
REACH SVHC: Not Reviewed
Low-Halogen Status: Not Reviewed

[Product Compliance Statement](#)

Application Tooling [FAQ](#)

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)

Part Detail

General

Status	Active
Category	Molex Parts
Series	130050
UPC	78678848338

Physical

Net Weight	4.530/g
------------	---------

Material Info

Old Part Number	ENP1135M050
-----------------	-------------

Molex Connectors

- Wire-to-Board
- Board-to-Board
- Wire-to-Wire
- Input/Output (IO)
- FFC/FPC
- Sockets

Other Products

- Fiber Optic Products
- Antennas
- Industrial Automation
- Membrane Switches
- Copper Flex
- PCB Assemblies
- Woodhead Electrical
- Solid State Lighting

Resources

- Contact Us
- Catalog
- Cross-Reference
- Industries
- Literature
- Product Name

Company Info

- About Us
- Careers
- ecocare
- Investors
- Press Room
- Shows & Events
- Supplier Portal

Other Info

- Feedback
- Help
- Legal Disclaimer
- View Mobile Site
- Privacy Policy
- Sitemap

Stay Connected with Molex: