



D31C Product Details

[Share](#) | [Print](#) | [Email](#)


✔ **Active**

Contactors

D31C (FAA/PMA)=RELAY
D31C (1616049-1)
 TE Internal Number: 1616049-1

Product Highlights [View All](#)

- Contactor Type = Sealed
- D-31 Series
- DC Actuating System
- 3 Poles
- Contact - Arrangement = 3PDT-NO

- [Pricing & Availability](#)
- [Request Sample](#)
- [Add to My Part List](#)
- [Buy Product through Distributor](#)

[Feedback](#)

[Documents](#) | [Features](#) | [Compliance](#)

Please Note:
 Use the Product Drawing for all design activity

Product Type Features	
Contactor Type	Sealed
Terminal Configuration	1/4-28-UNF-2A Stud
Mechanical Attachment	
Mounting Plate	With
Electrical Characteristics	
Actuating System [?]	DC
Contact Rating	115A
Coil - Rated Voltage (VDC) [?]	18 - 28
Coil Voltage, Max. (VDC) [?]	28
Frequency	400 Hz
Contact - Limiting Continuous Current-obs	Continuous
Termination Features	
Coil Termination	6-32 UNC-2A Stud

Body Features	
Torque	56 In-lbs (Mains) 7.5 In-lbs (Coil, Aux)
Arc Cover	With
Mount Type	Chassis
Contact Features	
Number of Poles [?]	3
Configuration Features	
Contact - Arrangement [?]	3PDT-NO
Industry Standards	
RoHS/ELV Compliance [?]	Not ELV/RoHS compliant
Lead Free Solder Processes [?]	Not relevant for lead free process
Other	
Series	D-31
Brand	Hartman

Related Products

Not quite the product you're looking for?
[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)