

DPL12H2424A20FG Product Details

[Share](#) | [Print](#) | [Email](#)


Active

Variable Resistors

LED ENCODER 12MM HORIZ DET GREEN
DPL12H2424A20FG (1-1879749-0)
 TE Internal Number: 1-1879749-0

Product Highlights [View All](#)

- Encoder
- Resistor Type = LED Encoder
- DPL12 Series
- Sections = Single
- Not Sealed

- [Pricing & Availability](#)
- [Request Sample](#)
- [Add to My Part List](#)
- [Buy Product through Distributor](#)

Feedback

[Documents](#) | [Features](#) | [Compliance](#)

Please Note:
Use the Product Drawing for all design activity

Product Type Features	
Product Type	Encoder
Resistor Type	LED Encoder
Sealed	No
Mount Angle	Horizontal

Termination Features	
Termination Type	PCB Terminations
Termination Post Orientation	5.0 x 2.5

Body Features	
Shaft Style	Flatted, M7 x 5mm Bush
Package, Component Size	14.0 x 13.2

Configuration Features	
Sections	Single
Adjustment Location	Side
Adjustment Style	Spindle
Operating Function	Continuous

Industry Standards	
RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Not reviewed for lead free solder process
RoHS/ELV Compliance History	Always was RoHS compliant

Other	
Series	DPL12
Brand	Citec

Related Products

Not quite the product you're looking for?
[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)