



# 208M814-19C10 Product Details

[Share](#) | [Print](#) | [Email](#)


✔ Active

## Braid, Fixed, Spin and Tinel Lock Adapters

208M814-19C10

**208M814-19C10**

TE Internal Number: F91992-000

**Product Highlights** [View All](#)

- Applies To Cable
- Military Style Number = MIL-DTL-38999
- Style = Braided
- Connector Code = 40
- 45°

[Pricing & Availability](#) >

[Request Sample](#) >

[Add to My Part List](#) +

[Buy Product through Distributor](#) >

Feedback

[Documents](#) | [Features](#) | [Compliance](#)

**Please Note:**

Use the Product Drawing for all design activity

Product Type Features	
Style	Braided
Angle	45°
Connector Shell Size	14
Finish	Electroless Nickel
Color	Bright
Dimensions	
Boot Diameter (mm [in])	27.46 [1.080]
Cable Diameter Range (mm [in])	11.00 - 18.20 [0.430 - 0.720]
Body Features	
Connector Code	40
Material	Aluminum Alloy

Configuration Features	
Braid	Preattached Single 36 AWG Braid
Industry Standards	
Government/Industry Qualification	No
Military Style Number	MIL-DTL-38999
RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant
Conditions for Usage	
Applies To	Cable
Other	
Brand	Raychem
Comment	For specific shell size information, refer to "Hardware" or Catalog.

**Related Products**

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

**Corporate Information**

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

**Quick Links**

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

**Customer Support**

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

**Keep Me Informed**

