



# 7022WCIMT Product Details

[Share](#) | [Print](#) | [Email](#)


Active

## Time Delay Relays

7022WCIMT=96VDC 1.5-15 SECS

7022WCIMT (2-1437490-4)

TE Internal Number: 2-1437490-4

### Product Highlights [View All](#)

- 7000 Electropneumatic Timing - Industrial Series
- Input Voltage = 96 VDC
- Contact - Arrangement = 2 Form C, DPDT, 2 C/O
- Contact Rating = 10A @ 240 VAC
- Mounting Options = Mounting Bracket

[Pricing & Availability](#)
[Request Sample](#)
[Add to My Part List](#)
[Buy Product through Distributor](#)
[Feedback](#)
[Documents](#)
[Features](#)
[Compliance](#)

#### Please Note:

Use the Product Drawing for all design activity

#### Product Type Features

<b>Option</b>	Tamper-Proof Cap - Transparent, Dust-Tight Gasketing, Auxilliary switch, two step timing
---------------	--

#### Mechanical Attachment

<b>Mounting Options</b>	Mounting Bracket
-------------------------	------------------

#### Electrical Characteristics

<b>Input Voltage (VDC)</b>	96
<b>Contact Rating</b>	10A @ 240 VAC

#### Termination Features

<b>Termination Type</b>	Screw Terminal
-------------------------	----------------

#### Dimensions

<b>Approx. Dimensions (L x W x H) (mm [in])</b>	114.80 x 65.30 x 71.90 [4.523 x 2.572 x 2.832]
---	--

#### Contact Features

<b>Delay Time</b>	1.5 seconds to 15 seconds
<b>Type of Control</b>	Knob
<b>Repeatability, Max.</b>	± 5%

#### Configuration Features

<b>Contact - Arrangement</b>	2 Form C, DPDT, 2 C/O
<b>Multiple Timing Ranges</b>	Without

#### Industry Standards

<b>Approved Standards</b>	CE Approved, CSA Certified, UL Listed
<b>RoHS/ELV Compliance</b>	Not ELV/RoHS compliant
<b>Lead Free Solder Processes</b>	Not relevant for lead free process

#### Conditions for Usage

<b>Temperature Range (°C)</b>	-30 - +75
-------------------------------	-----------

#### Operation/Application

<b>Mode of Operation</b>	Off-Delay
--------------------------	-----------

#### Other

<b>Series</b>	7000 Electropneumatic Timing - Industrial
<b>Brand</b>	Agastat

#### Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

#### Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

#### Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

#### Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

#### Keep Me Informed

