



7022WCV Product Details

[Share](#) | [Print](#) | [Email](#)


✔ Active

Time Delay Relays

7022WCV=96V DC 1.5-15 SEC

7022WCV (2-1437490-7)

TE Internal Number: 2-1437490-7

Product Highlights [View All](#)

- 7000 Electropneumatic Timing - Industrial Series
- Input Voltage = 96 VDC
- Contact - Arrangement = 2 Form C, DPDT, 2 C/O
- Contact Rating = 10A @ 240 VAC
- Mounting Options = Mounting Bracket

[Pricing & Availability](#) ➤

[Request Sample](#) ➤

[Add to My Part List](#) +

[Buy Product through Distributor](#) ➤

Feedback

[Documents](#) | [Features](#) | [Compliance](#)

Please Note:

Use the Product Drawing for all design activity

Product Type Features

Option	Transient/Surge Protection
--------	----------------------------

Mechanical Attachment

Mounting Options	Mounting Bracket
------------------	------------------

Electrical Characteristics

Input Voltage (VDC)	96
Contact Rating	10A @ 240 VAC

Termination Features

Termination Type	Screw Terminal
------------------	----------------

Dimensions

Approx. Dimensions (L x W x H) (mm [in])	114.80 x 65.30 x 71.90 [4.523 x 2.572 x 2.832]
--	--

Contact Features

Delay Time	1.5 seconds to 15 seconds
Type of Control	Knob
Repeatability, Max.	± 5%

Configuration Features

Contact - Arrangement ?	2 Form C, DPDT, 2 C/O
--	-----------------------

Multiple Timing Ranges	Without
------------------------	---------

Industry Standards

Approved Standards	CE Approved, CSA Certified, UL Listed
--------------------	---------------------------------------

RoHS/ELV Compliance ?	Not ELV/RoHS compliant
--	------------------------

Lead Free Solder Processes ?	Not relevant for lead free process
---	------------------------------------

Conditions for Usage

Temperature Range (°C)	-30 - +75
------------------------	-----------

Operation/Application

Mode of Operation	Off-Delay
-------------------	-----------

Other

Series	7000 Electropneumatic Timing - Industrial
--------	---

Brand	Agastat
-------	---------

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

