


[Relays, Contactors & Switches](#) > [Switches](#) > [Pushbutton Switches](#)

AV19 DPL 0.4VA POWER LED BLUE 12V



Alcoswitch | [Alcoswitch AV](#)

TE Part # **AV1921P712R04**
TE Internal #: **7-2213766-8**

Configuration (Pole-Throw) : **Double Pole - Double Throw**

Number of Actuators : **Single**

Actuator Profile : **Flush**

Bushing Style : **Threaded**

Illuminated : **Yes**

[Similar Products](#)

ORDER SAMPLES

Compatible Parts & Tooling

SHOP OUR DISTRIBUTORS

North America

Request pricing, availability and customization options

CONTACT US

We are here to help!

Get in touch with our product experts.



CHAT WITH US



EMAIL US



CALL US

Please give us feedback:
Did you find what you need on this page?

YES

NO

DOCUMENTS

FEATURES

PRODUCT COMPLIANCE

Product Drawings **AV19 DPL 0.4VA POWER LED BLUE 12V**
 AV19 DPL 0.4VA POWER LED BLUE 12V English

CAD Files **3D PDF**
 3D_CVM_CVM_7-2213766-8_A.pdf 3D
Customer View Model
 ENG_CVM_CVM_7-2213766-8_A.2d_dxf.zip
English
 ENG_CVM_CVM_7-2213766-8_A.3d_igs.zip
English
 ENG_CVM_CVM_7-2213766-8_A.3d_stp.zip
English

Agency Approvals **UL Report**
 ENG_AAD_UL_E46765_20030916__A.pdf
English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features
Dust Proof : **Yes**
Illuminated : **Yes**
Actuator Style : **Round**
Product Type : **Switch**



Switch Type : **Pushbutton**

Configuration Features

Configuration (Pole-Throw) :

Double Pole - Double Throw

Number of Actuators : **Single**

Snap Action : **Without**

Support Bracket : **Without**

Tactile : **No**

Operating Function : **Push-On/Push-Off**

Detent Style : **Audible**

ESD Grounding Terminal : **Without**

Electrical Characteristics

Voltage Rating (VAC): **250**

Body Features

Case Material : **PBT**

Actuator Profile : **Flush**

Bushing Style : **Threaded**

Contact Features

Contact Current Rating (A):

.4

Switch Contact Plating Material :

Gold

Termination Features

Termination Type : **Wire Lugs**

Mechanical Attachment

Mounting Type : **Panel**

Mounting Angle : **Vertical**

Housing Features

Process Sealed : **Yes**

Dimensions

Bushing Length (in): **19**

Statement of Compliance

[Statement of Compliance pdf](#)





Pushbutton Switches (705)

ABOUT TE CONNECTIVITY

- [Our Company](#)
- [Events](#)
- [TE News Center](#)
- [Careers](#)
- [Investors](#)
- [Corporate Responsibility](#)
- [Terms and Conditions of Sale](#)

FOR PARTNERS

- [Distributors](#)
- [Suppliers](#)

CUSTOMER SUPPORT

- [Email or Call Us](#)
- [Find Authorized Distributors](#)
- [Shop Online in the TE Store](#)
- [Product FAQs](#)

CALL US

SELECT LANGUAGE

- [United States](#)
- [Germany](#)
- [China \(中文\)](#)
- [Japan \(日本語\)](#)

- [Afghanistan \(EN\)](#)
- [Find Your Country/Region](#)

Need help?



Our team is on stand-by and ready to help with your order.

CHAT NOW

