


[Relays, Contactors & Switches](#) > [Switches](#) > [Pushbutton Switches](#)

# AV19 DPM 5A POWER LED YELLOW 24V



Alcoswitch | Alcoswitch AV

TE Part # **AV1920P524Q04**

TE Internal #: **5-2213766-1**

Configuration (Pole-Throw) : **Double Pole - Single Throw**

Number of Actuators : **Single**

Actuator Profile : **Flush**

Bushing Style : **Threaded**

Illuminated : **Yes**

[Similar Products](#)

**ORDER SAMPLES**

**Compatible Parts & Tooling**

### SHOP OUR DISTRIBUTORS

North America

[See all price breaks](#)

Distributor	1	10,000	Buy
<b>DIGI-KEY ELECTRONICS</b>	\$16.580	\$12.215	<a href="#">Visit Site</a>
99 in stock			
<b>NEWARK ELEMENT14</b>	\$9.280	\$9.280	<a href="#">Visit Site</a>
50 in stock			

### We are here to help!

Get in touch with our product experts.

**CHAT WITH US**

**EMAIL US**

**CALL US**

Please give us feedback:  
Did you find what you need on this page?

**YES**

Feedback

#### DOCUMENTS

#### FEATURES

#### PRODUCT COMPLIANCE

Product Drawings **AV19 DPM 5A POWER LED YELLOW 24V**  
[Download AV19 DPM 5A POWER LED YELLOW 24V](#)  
 English

CAD Files **3D PDF**  
[Download 3D\\_CVM\\_CVM\\_5-2213766-1\\_A.pdf](#) 3D  
 Customer View Model  
[Download ENG\\_CVM\\_CVM\\_5-2213766-1\\_A.2d\\_dxf.zip](#)  
 English  
[Download ENG\\_CVM\\_CVM\\_5-2213766-1\\_A.3d\\_igs.zip](#)  
 English  
[Download ENG\\_CVM\\_CVM\\_5-2213766-1\\_A.3d\\_stp.zip](#)  
 English

Catalog Pages/Data Sheets [Download ENG\\_DS\\_1-1773878-3\\_Alcoswitch\\_AntiVandal\\_0517.pdf](#) English

Agency Approvals **UL Report**  
[Download ENG\\_AAD\\_UL\\_E46765\\_20030916\\_\\_A.pdf](#)  
 English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.



Product Type  
Features

Dust Proof : **Yes**  
Illuminated : **Yes**  
Actuator Style : **Round**  
Product Type : **Switch**  
Switch Type : **Pushbutton**

Configuration  
Features

Configuration (Pole-Throw) :  
**Double Pole - Single  
Throw**  
Number of Actuators : **Single**  
Snap Action : **Without**  
Support Bracket : **Without**  
Tactile : **No**  
Operating Function : **Momentary**  
Detent Style : **Audible**  
ESD Grounding Terminal : **Without**

Electrical  
Characteristics

Voltage Rating (VAC): **250**

Body Features

Case Material : **PBT**  
Actuator Profile : **Flush**  
Bushing Style : **Threaded**

Contact Features

Contact Current Rating (A):  
**5**  
Switch Contact Plating Material :  
**Silver**

Termination  
Features

Termination Type : **Wire Lugs**

Mechanical  
Attachment

Mounting Type : **Panel**  
Mounting Angle : **Vertical**

Housing Features

Process Sealed : **Yes**

Dimensions

Bushing Length (in): **19**

Statement of  
Compliance

[Statement of Compliance pdf](#)



**Pushbutton Switches**  
(705)

**ABOUT TE CONNECTIVITY**

- [Our Company](#)
- [Events](#)
- [TE News Center](#)
- [Careers](#)
- [Investors](#)
- [Corporate Responsibility](#)
- [Terms and Conditions of Sale](#)

**FOR PARTNERS**

- [Distributors](#)
- [Suppliers](#)

**CUSTOMER SUPPORT**

- [Email or Call Us](#)
- [Find Authorized Distributors](#)
- [Shop Online in the TE Store](#)
- [Product FAQs](#)

**CALL US**

**SELECT LANGUAGE**

- [United States](#)
- [Germany](#)
- [China \(中文\)](#)
- [Japan \(日本語\)](#)
- [Afghanistan \(EN\)](#)
- [Find Your Country/Region](#)

**Need help?** ×

Our team is on stand-by and ready to help with your order.

**CHAT NOW** >