


[Relays, Contactors & Switches](#) > [Switches](#) > [Pushbutton Switches](#)

# AV19 DPM 5A FIX RING LED RED 24V



Alcoswitch | [Alcoswitch AV](#)

TE Part # **AV1920R324Q04**

TE Internal #: **4-2213764-7**

Configuration (Pole-Throw) : **Double Pole - Single Throw**

Number of Actuators : **Single**

Actuator Profile : **Flush**

Bushing Style : **Threaded**

Illuminated : **Yes**

[Similar Products](#)

**ORDER SAMPLES**

**Compatible Parts & Tooling**

## SHOP OUR DISTRIBUTORS

North America

Request pricing, availability and customization options

**CONTACT US**

## We are here to help!

Get in touch with our product experts.



**CHAT WITH US**



**EMAIL US**



**CALL US**

Please give us feedback:  
Did you find what you need on this page?

**YES**

**NO**

### DOCUMENTS

### FEATURES

### PRODUCT COMPLIANCE

#### Product Drawings

AV19 DPM 5A FIX RING LED RED 24V

[AV19 DPM 5A FIX RING LED RED 24V](#) English

#### CAD Files

3D PDF

[3D\\_CVM\\_CVM\\_4-2213764-7\\_A.pdf](#) 3D

Customer View Model

[ENG\\_CVM\\_CVM\\_4-2213764-7\\_A.2d\\_dxf.zip](#)

English

[ENG\\_CVM\\_CVM\\_4-2213764-7\\_A.3d\\_igs.zip](#)

English

[ENG\\_CVM\\_CVM\\_4-2213764-7\\_A.3d\\_stp.zip](#)

English

#### Agency Approvals

UL Report

[ENG\\_AAD\\_UL\\_E46765\\_20030916\\_\\_A.pdf](#)

English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

#### Product Type Features

Dust Proof : **Yes**

Illuminated : **Yes**

Actuator Style : **Round**

Product Type : **Switch**



Switch Type : **Pushbutton**

Configuration Features

Configuration (Pole-Throw) :

**Double Pole - Single Throw**

Number of Actuators : **Single**

Snap Action : **Without**

Support Bracket : **Without**

Tactile : **No**

Operating Function : **Momentary**

Detent Style : **Audible**

ESD Grounding Terminal : **Without**

Electrical Characteristics

Voltage Rating (VAC): **250**

Body Features

Case Material : **PBT**

Actuator Profile : **Flush**

Bushing Style : **Threaded**

Contact Features

Contact Current Rating (A):

**5**

Switch Contact Plating Material :

**Silver**

Termination Features

Termination Type : **Wire Lugs**

Mechanical Attachment

Mounting Type : **Panel**

Mounting Angle : **Vertical**

Housing Features

Process Sealed : **Yes**

Dimensions

Bushing Length (in): **19**

Statement of Compliance

[Statement of Compliance pdf](#)





## Pushbutton Switches (705)

### ABOUT TE CONNECTIVITY

- [Our Company](#)
- [Events](#)
- [TE News Center](#)
- [Careers](#)
- [Investors](#)
- [Corporate Responsibility](#)
- [Terms and Conditions of Sale](#)

### FOR PARTNERS

- [Distributors](#)
- [Suppliers](#)

### CUSTOMER SUPPORT

- [Email or Call Us](#)
- [Find Authorized Distributors](#)
- [Shop Online in the TE Store](#)
- [Product FAQs](#)

### CALL US

#### SELECT LANGUAGE

- [United States](#)
- [Germany](#)
- [China \(中文\)](#)
- [Japan \(日本語\)](#)

- [Afghanistan \(EN\)](#)
- [Find Your Country/Region](#)

Need help?



Our team is on stand-by and ready to help with your order.

CHAT NOW

