



W-063-07 Product Details

[Share](#) | [Print](#) | [Email](#)


Active

SolderSleeve Wire Splices

W-063-07

W-063-07

TE Internal Number: 695362-000

Product Highlights [View All](#)

- Wire Splice
- Splice Type = SolderSleeve
- Fluid Resistance = Immersion
- Wire Temperature Rating Range (Max.) = At Least 125 °C
- Inside Diameter = 4.40 mm

[Pricing & Availability](#)
[Request Sample](#)
[Add to My Part List](#)
[Buy Product through Distributor](#)
[Feedback](#)
[Documents](#)
[Features](#)
[Compliance](#)

Please Note:

Use the Product Drawing for all design activity

Product Type Features

Product Type	Wire Splice
Splice Type	SolderSleeve

Termination Features

Connection Type	SolderSleeve
-----------------	--------------

Dimensions

Inside Diameter (mm [in])	4.40 [0.173]
Length (mm [in])	16.40 [0.646]

Industry Standards

RoHS/ELV Compliance	Not ELV/RoHS compliant
Lead Free Solder Processes	Not relevant for lead free process

Environmental

Fluid Resistance	Immersion
Operating Temperature (Max.) (°C)	150

Conditions for Usage

Wire Temperature Rating Range (Max.)	At Least 125 °C
--------------------------------------	-----------------

Operation/Application

Application	SolderSleeve Shield Terminator
-------------	--------------------------------

Other

Brand	Raychem
-------	---------

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [Global Accessibility Statement](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

