



+ CONNECTORS

SCREENED



✓ Active

TE CONNECTIVITY (TE)

## TXR30AB00-2412AI2

Raychem | TCR , Terminator

TXR30AB00-2412AI2

TE Internal Number: 877615-000

Alias ID: 3-1196825-1

Not EU RoHS Compliant

Not EU ELV Compliant

Adapter Angle 00

Cable Diameter Range 95 – 152 mm [ 375 – 6 in ]

Adapter Entry Size 12

TE Adapter Code 30

Material Aluminum

↓ **PRODUCT DRAWING**  
English

### DOCUMENTATION

Product Drawings

#### Tinel Lock Backshell

PDF

English

Product Specifications

Product Specification

#### General Information Package For Tinel-Lock Adapters

PDF

English

#### Adapter Finish Specifications

PDF

English

## Product Environmental Compliance

REACH Substance Communication Document

### RSCD\_Cadmium

PDF

English

## FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

### Product Type Features

**Adapter Angle** 00

**Style** Pre-Braided Tinel-Lock

**Termination Device Type** Side-Entry Tinel-Lock Ring, Tinel-Lock Ring

**Connector Shell Size** 25, G

### Configuration Features

**Braid** 36 Single

### Body Features

**Adapter Entry Size** 12

**TE Adapter Code** 30

**Material** Aluminum

**Adapter Plating Material** Cadmium per SAE AMS-QQ-P-416, Type II, Class 3, over appropriate under plate, per SAE AS85049 (500 Hour Salt Spray)

### Dimensions

**Cable Diameter Range** 95 – 152 mm [ 375 – 6 in ]

### Industry Standards

**Connector Detail Specification Number** M28840/10, M28840/11, M28840/14, M28840/16

### Other

**Connector General Specification Number** MIL-DTL-28840 Class D,DS

## PRODUCT COMPLIANCE



Statement of Compliance

### Statement of Compliance

PDF

