



1-1825027-1 Product Details

Share | Print | Email



1-1825027-1

TE Internal Number: 1-1825027-1

Active

View 3D PDF

Pushbutton Switches

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Switch
- Tactile
- Single Pole - Single Throw Configuration (Pole-Throw)
- Contact Rating = 50mA
- Operating Function = Off [On]

[View all Features](#)

Quick Links

- ▶ Pricing & Availability
- ▶ Search for Tooling
- ▶ Product Feature Selector
- ▶ Contact Us About This Product

[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- MICRO-MINIATURE PUSHBUTTON SWITCH (PDF, English)

Catalog Pages/Data Sheets:

- SWITCHES_CORE_PROGRAM_CATALOG (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: (CAD Format & Compression Information)

- 2D Drawing (DXF, Version G1)
- 3D Model (IGES, Version G1)
- 3D Model (STEP, Version G1)

Related Products:

- Tooling

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Switch
- Tactile = Yes
- Series = FSMRAJ
- Mount Angle = Right Angle
- Termination Type = Printed Circuit
- Actuator Style = Round

Electrical Characteristics:

- Contact Rating = 50mA

Dimensions:

- Actuator Length (mm [in]) = 5.74 [0.226]

Body Features:

- Mount Style = Through-Hole
- Actuator Profile = Extended
- Actuator Color = Black
- Case Material = Nylon
- Actuator Material = PBT

Contact Features:

- Contact Plating = Silver
- Contact Base Material = Copper Alloy

Housing Features:

- Process Sealed = No
- Low Profile = No

Configuration Features:

- Configuration (Pole-Throw) = Single Pole - Single Throw
- Operating Function = Off [On]
- Ganged = No
- ESD Grounding Terminal = Without
- Number of Actuators = Single
- Illuminated = No
- Dust Proof = No
- Support Bracket = With
- Snap Action = Without
- Tactile Feel = With
- Switch Height (mm [in]) = 7.00 [0.276]

Industry Standards:

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- Temperature Rating = Standard

Operation/Application:

- Actuator Force (g [oz]) = 160.00 [5.648]

Packaging Features:

- Packaging Method = Loose Piece

Other:

- Brand = TE Connectivity
- Comment = (On) indicates momentary position.

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

