



Edit Profile

Change Password

| Logout |_My Parts (0 items)

×

- Products
- Industry Solutions
- CAREERS
- Resources
- Find Distributor
- Contact Molex

Enter Part No. or Keyv Search

Product Name Index





Part Number: 130008-0077

MC 10P FP 15M 10 MICRO MPIS PV



Series image - Reference only

Status: Active Series: <u>130008</u> Category: Molex Parts

Engineering/Old PN: 301000A04M150

Product Environmental Compliance

EU ELV:Not Reviewed

EU RoHS:Not Reviewed

EU RoHS Phthalates:Not Reviewed

China RoHS:Not Reviewed

REACH SVHC: Not Reviewed

Low-Halogen Status: Not Reviewed

Part Detail

General

Status Active
Category Molex Parts
Series 130008
UPC 78678845092
Agency Certification

Please find UL Certificates by searching the UL Database using the Molex Series Number. Click here to visit the UL

Database

CSA LR6837

Material Info

Engineering Number 301000A04M150

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

Products+

- Product Categories
- Product Index
- Industries

Quick Links+

- Company Information
- Contact Molex
- Cross-Reference
- Koch Industries
- Investor Relations
- Literature
- Press Room / Press Releases
- Sitemap • Terms & Conditions

Resources+

- Supply Chain Transparency
- Business Continuity
- Compliance
- ecocare
- Feedback | Help
- Jobs
- Legal | Trademarks
- Supplier Portal
- Privacy Policy
- Tradeshows

Stay Connected



















Molex is a registered trademark of Molex, LLC in the United States of America and may be registered in other countries; all other trademarks listed herein belong to their respective owners.

© Copyright 2018