



+ RELAYS, CONTACTORS & SWITCHES

PUSHBUTTON SWITCHES



✓ Active

TE CONNECTIVITY (TE)

AV16 SPM 0.4VA FIX RING LED BLUE 12V

Alcoswitch | Alcoswitch AV

AV1610R712R04

TE Internal Number: 2213774-9

EU RoHS Compliant

EU ELV Compliant

Configuration (Pole-Throw) Single Pole - Single Throw

Number of Actuators Single

Actuator Profile Flush

Bushing Style Threaded

Illuminated Yes

↓ **PRODUCT DRAWING**
English

↓ **3D PDF**

DOCUMENTATION

Product Drawings

ANTI-VANDA SWITCH 16mm FIXED RING LED

PDF

English

CAD Files

3D PDF

PDF

3D

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Illuminated Yes

Actuator Style Round

Product Type Switch

Switch Type Pushbutton

Dust Proof Yes

Configuration Features

Configuration (Pole-Throw) Single Pole - Single Throw

Number of Actuators Single

Snap Action Without

Support Bracket Without

Tactile No

Operating Function Momentary

ESD Grounding Terminal Without

Detent Style Audible

Electrical Characteristics

Voltage Rating (VDC) 36

Body Features

Actuator Profile Flush

Bushing Style Threaded

Case Material PBT

Contact Features

Contact Current Rating (A) .4

Contact Plating Gold

Termination Features

Termination Type Wire Lugs

Mechanical Attachment

Mounting Type Panel

Mounting Angle Vertical

Housing Features

Process Sealed Yes

Dimensions

Bushing Length (in) 16

Statement of Compliance

Statement of Compliance

PDF