




**+** RELAYS, CONTACTORS & SWITCHES

PUSHBUTTON SWITCHES



✓ Active

TE CONNECTIVITY (TE)

## AV19 SPL 0.4VA POWER LED RED 24V

Alcoswitch | Alcoswitch AV

AV1911P324R04

TE Internal Number: 2-2213766-8

EU RoHS Compliant

EU ELV Compliant

**Configuration (Pole-Throw)** Single Pole - Double Throw

**Number of Actuators** Single

**Actuator Profile** Flush

**Bushing Style** Threaded

**Illuminated** Yes

[↓](#) **PRODUCT DRAWING**  
English

[↓](#) **3D PDF**

### DOCUMENTATION

Product Drawings

#### **ANTI-VANDAL SWITCH 19mm POWER LOGO LED**

PDF

English

CAD Files

#### **3D PDF**

PDF

3D

#### **Customer View Model**

2D\_DXF.ZIP

English

#### **Customer View Model**

3D\_IGS.ZIP

English

### Customer View Model

3D\_STP.ZIP

English

---

Agency Approvals

UL Report

### Anti Vandal Switches

PDF

English

---

## FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

---

### Product Type Features

**Illuminated** Yes

**Actuator Style** Round

**Product Type** Switch

**Switch Type** Pushbutton

**Dust Proof** Yes

---

### Configuration Features

**Configuration (Pole-Throw)** Single Pole - Double Throw

**Number of Actuators** Single

**Snap Action** Without

**Support Bracket** Without

**Tactile** No

**Operating Function** Push-On/Push-Off

**ESD Grounding Terminal** Without

**Detent Style** Audible

---

### Electrical Characteristics

**Voltage Rating (VAC)** 250

---

### Body Features

**Actuator Profile** Flush

**Bushing Style** Threaded

**Case Material** PBT

---

### Contact Features

**Contact Current Rating (A)** .4

**Contact Plating** Gold

---

### Termination Features

**Termination Type** Wire Lugs

---

Mechanical Attachment

**Mounting Type** Panel

**Mounting Angle** Vertical

---

Housing Features

**Process Sealed** Yes

---

Dimensions

**Bushing Length (in)** 19

Statement of Compliance

**Statement of Compliance**

PDF