


TIME DELAY RELAYS



✓ Active

TE CONNECTIVITY

7012WCL=RLY,STD,ON,2P,96VDC,1

3-1437488-5

TE Internal Number: 3-1437488-5
 Alias ID: 7012WCL

[Not EU RoHS or ELV Compliant](#)
[Find Compliant Alternatives](#)

Type of Control **Knob**

Input Voltage(VDC) **96**

Contact Current Rating(A) **10A@240VAC**

Mode of Operation **On-Delay**

Delay Time **1.5 – 15 seconds**

[> See All Features](#)

North America ▼

[SAVE TO LIST](#)



[FIND SIMILAR PRODUCTS](#)



Contact us to request pricing, availability and customization options.

[REQUEST ADDITIONAL INFORMATION](#)



DOCUMENTATION FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features

Relay Type	Time Delay
Product Category	Electromechanical Relays
Product Type	Relay

Configuration Features

Multiple Timing Ranges	Without
------------------------	----------------

Electrical Characteristics

Input Voltage(VDC)	96
Actuating System	DC

Contact Features

Type of Control	Knob
Contact Current Rating(A)	10A@240VAC
Delay Time	1.5 – 15 seconds
Contact Arrangement	2 Form C, DPDT, 2 C/O

Termination Features

Termination Type	Screw Terminal
------------------	-----------------------

Mechanical Attachment

Mounting Type	Mounting Bracket
---------------	-------------------------

Dimensions

Dimensions (L x W x H) (Approximate)	114.8 x 82.55 x 78.48mm[4.52 x 3.25 x 3.09 in]
--------------------------------------	---

Usage Conditions

Operating Temperature Range(°C)	-30 – 75
---------------------------------	-----------------

Operation/Application

Mode of Operation	On-Delay
-------------------	-----------------

Other

Repeatability (Max)	±5%
Option	Auxiliary Switch - Instant Transfer

Product Compliance

[Statement of Compliance](#)
 PDF

[VIEW ALL PRODUCT COMPLIANCE](#)

COMPATIBLE

No compatible products found for 3-1437488-5