




NECTOR | NECTOR S

TE Internal #: 1740316-1

Plug & Socket Lighting Connector Accessories, Coding Ring, 7
Position, Power, NECTOR S

[View on TE.com >](#)

Connectors > Lighting Connectors > Plug & Socket Connector Accessories



Lighting Connector Accessory Type: **Coding Ring**

Number of Positions: **7**

Sealable: **No**

Circuit Application: **Power**

Features

Product Type Features

Product Type	Accessory
Lighting Connector Accessory Type	Coding Ring
Sealable	No

Configuration Features

Number of Positions	7
---------------------	---

Housing Features

Housing Color	Red
---------------	-----

Operation/Application

Circuit Application	Power
---------------------	-------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2022 (224)

Candidate List Declared Against: JUNE 2022 (224)

Does not contain REACH SVHC

Halogen Content

Not Low Halogen - contains Br or Cl > 900 ppm.

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 1740317-1
NECTOR S DISTRIBUTOR ASSY 6 POS
WHITE




TE Part # 1740317-2
NECTOR S DISTRIBUTOR ASSY 7 POS
WHITE


Also in the Series | NECTOR S




Insertion & Extraction Tools(3)



Lighting Cable Assemblies(1)



Plug & Socket Lighting Connector
Accessories(57)



Plug & Socket Lighting Connectors(54)

Documents

[Product Drawings](#)
[NECTOR S CODING RING](#)



English

CAD Files

Customer View Model

[ENG_CVM_CVM_1740316-1_C.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1740316-1_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1740316-1_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[NECTOR_S_LINE_CONNECTOR_BROCHURE](#)

English