

2-2132074-0 ✓ ACTIVE




SL-156

TE Internal #: 2-2132074-0

PCB Latches, Locks & Retainers, Retainer, 20 Position, .156 in [3.96 mm] Centerline, 1 Row, -67 – 221 °F [-55 – 105 °C], SL-156

[View on TE.com >](#)

Connectors > PCB Connectors > PCB Connector Accessories > PCB Connector Hardware > PCB Latches, Locks & Retainers



Connector & Contact Retention Accessory Type: **Retainer**

Number of Positions: **20**

Centerline (Pitch): **3.96 mm [.156 in]**

Number of Rows: **1**

Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**

Features

Product Type Features

| | |
|--|----------|
| Connector & Contact Retention Accessory Type | Retainer |
|--|----------|

Configuration Features

| | |
|---------------------|----|
| Number of Positions | 20 |
| Number of Rows | 1 |

Body Features

| | |
|--------------------------|-------|
| Primary Product Material | Valox |
| Primary Product Color | Black |

Housing Features

| | |
|--------------------|-------------------|
| Centerline (Pitch) | 3.96 mm [.156 in] |
|--------------------|-------------------|

Usage Conditions

| | |
|-----------------------------|-----------------------------|
| Operating Temperature Range | -55 – 105 °C [-67 – 221 °F] |
|-----------------------------|-----------------------------|

Industry Standards

| | |
|------------------------|-------------------------------|
| Glow Wire Rating | Standard Part - Not Glow Wire |
| UL Flammability Rating | UL 94V-0 |



Packaging Features

| | |
|--------------------|-----|
| Packaging Quantity | 200 |
| Packaging Method | Bag |

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC |
| Halogen Content | Not Low Halogen - contains Br or Cl > 900 ppm. |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

| | | | |
|---|---|--|---|
|  <p>TE Part # CAT-103156-WBHSM Receptacle Housing: Wire-to-Board, with Mating Alignment, SL156</p> |  <p>TE Part # 640254-1 KEYING PLUG .045 SQ PST CONN</p> |  <p>TE Part # CAT-103156-RECHS Connector Housing, Rectangular, 3.96 mm, 1 Row</p> |  <p>TE Part # 640255-1 KEYING PIN .045 SQ PST CONN</p> |
|---|---|--|---|


Also in the Series | SL-156



Insertion & Extraction Tools(1)



PCB Connector Keying(2)



PCB Latches, Locks & Retainers(1)



Rectangular Connector Housings(12)



Rectangular Connector Keying Plugs(1)



Wire-to-Board Connector Assemblies & Housings(158)



Wire-to-Board Connector Contacts(24)

Documents

Product Drawings

20Pos SL156 Contact Retainer

English

CAD Files

Customer View Model

[ENG_CVM_CVM_2-2132074-0_A.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2-2132074-0_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-2132074-0_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[7-1773461-7_SL-156_CONNECTOR_TPA_DEVICE](#)

English

Product Specifications

[Product Specification](#)

English

Product Environmental Compliance

[MD_2-2132074-0_102820112253](#)

2-2132074-0

PCB Latches, Locks & Retainers, Retainer, 20 Position, .156 in [3.96 mm] Centerline, 1 Row, -67 – 221 °F [-55 – 105 °C], SL-156



English

[MD_2-2132074-0_102820112253](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English