



**SPIRAP**

TE Internal #: 500013-1

Cable Tie Mounts & Accessories, Cable Tie Tool, Spiral, Product Width .125 in [3.18 mm], Nylon, Natural, Packaged Length 15.24 m [50 ft], Box, SPIRAP

[View on TE.com >](#)

Wire & Cable > Wire & Cable Accessories > Cable Tie Mounts & Accessories



Wire & Cable Accessory Type: **Cable Tie Tool**

Wire & Cable Mounting Type: **Spiral**

Adhesive Back: **Without**

Product Width: **3.18 mm [ .125 in ]**

Primary Product Material: **Nylon**

**Features**

**Product Type Features**

Product Type	Cable Wrap
Wire & Cable Accessory Type	Cable Tie Tool

**Body Features**

Primary Product Material	Nylon
Primary Product Color	Natural

**Mechanical Attachment**

Wire & Cable Mounting Type	Spiral
Adhesive Back	Without

**Dimensions**

Overall Outside Diameter	3.18 mm [.125 in]
Bundle Range Diameter	1.59 – 12.7 mm [.063 – .5 in]
Product Width	3.18 mm [.125 in]

**Packaging Features**

--	--



Packaged Length	15.24 m[50 ft]
-----------------	----------------

Packaging Method	Box
------------------	-----

### Other

Comment	SPIRAP Hand Tool is included with each box.
---------	---

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
--	--

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not applicable for solder process capability
---------------------------	--


#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



## Also in the Series | SPIRAP



## Documents

### Product Drawings

[SPIRAP, 1/8" NYLON, NAT, 50 FT](#)

English

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_500013-1\\_Z.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_500013-1\\_Z.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_500013-1\\_Z.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[SPIRAP PLASTIC CABLE WRAP TECHNICAL DATA SHEET](#)

English