

90760-2 ✓ ACTIVE

AMP


TE Internal #: 90760-2

Hand Crimping Tools, Commercial Crimp Tooling, Operator Releasable & Adjustable, Removable/Interchangeable, TE Product Specification (114-)

[View on TE.com >](#)



Application Tooling > Hand Crimping Tools



Tool Grade: **Commercial Crimp Tooling**

Ratchet Configuration: **Operator Releasable & Adjustable**

Die Sets Type: **Removable/Interchangeable**

Specification Type: **TE Product Specification (114-)**

TE Certification: **Upon Request for Fee**

Features

Other

| | |
|-----------------------------|-------------------------------------|
| Crimp Form-Wire Barrel Type | Open Barrel - F Crimp |
| Tool Grade | Commercial Crimp Tooling |
| Ratchet Configuration | Operator Releasable & Adjustable |
| Die Sets Type | Removable/Interchangeable |
| Specification Type | TE Product Specification (114-) |
| TE Certification | Upon Request for Fee |
| Power Technology Type | Battery, Electric, Manual |
| Tooling Type | Standard Die Envelope (SDE) Die Set |

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|--|
| EU RoHS Directive 2011/65/EU | Out of Scope |
| EU ELV Directive 2000/53/EC | Out of Scope |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Not reviewed for China RoHS compliance |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC |
| Halogen Content | Not Yet Reviewed for halogen content |

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2280380-1
KIT, BT, MICRO SDE, 110V



TE Part # 1-794407-1
MINI UMNL SOK 20-16 AWG AU LF



TE Part # 171638-1
MINI U-M-N-L PIN CONT. LP



TE Part # 171639-1
MINI U-M-N-L SOCKET LP



TE Part # 1-794407-0
MINI UMNL SOK 20-16 AWG AU LF



TE Part # 794406-3
MINI UMNL CONT 20-16AWG AU



TE Part # 794407-1
MINI UNML SCKT 20-16 AWG SN



TE Part # 794406-1
MINI UMNL CONT 20-16AWG SN



TE Part # 171636-1
MINI U-M-N-L PIN CONTACT



TE Part # 171637-1
MINI U-M-N-L SOCKET CONTACT



TE Part # 794407-4
MINI UNML SCKT 20-16 AWG SN



TE Part # 1-794406-0
MINI UMNL SOK 20-16 AWG AU LF



TE Part # 2280380-2
KIT, BT, MICRO SDE, 220V



TE Part # 794407-6
MINI UNML SCKT 20-16 AWG AU

TE Part # 171637-2
MINI U-M-N-L SOCKET CONT AS

TE Part # 794406-2
MINI UMNL CONT 20-16AWG UNPL

TE Part # 794407-2
MINI UNML SCKT 20-16AWG UNPLTD

TE Part # 794407-5
MINI UNML SCKT 20-16AWG UNPLTD

TE Part # 794407-7
MINI UNML SCKT CONT STRIP SN

TE Part # 794407-8
MINI UNML SCKT CONT STRIP UNPL

Documents

Datasheets & Catalog Pages

[1-1773865-2_1015_Commercial Manual Hand Tools](#)

English

Bottoming Dies

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

[Instruction Sheet \(U.S.\)](#)

English

[PRO-CRIMPER II Hand Tool Assembly 90760-1 w/Die Assembly 90760-2](#)

English