

91067-1 ✓ ACTIVE

TE Internal #: 91067-1

TE Internal Description: INSERTION/EXTRACTION TOOL

Mil-Spec: [M81969/1-04]

[View on TE.com >](#)



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-1757824-2
AMPLIMITE,ASY,RCPT,STD,90,ZN,6,
CONT



TE Part # 204520-2
RECEPT ASSY,78 POSN,AMPLIMITE



TE Part # 204514-2
RECEPT ASSY,26 POSN,AMPLIMITE



TE Part # 204516-2
RECEPT ASSY,SZ 3,AMPLIMITE



TE Part # 204519-2
AMPLIMITE,ASY,PLUG,STD,90,4



TE Part # 204517-2
AMPLIMITE,ASY,PLUG,STD,90,3



TE Part # 204515-2
AMPLIMITE,ASY,PLUG,STD,90,2



TE Part # 207684-1
AMPLIMITE,SKT CONT,SZ 22



TE Part # 207684-3
AMPLIMITE,SKT CONT,SZ 22



TE Part # 207683-2
AMPLIMITE,PIN CONT,SZ 22



TE Part # 1-1757824-0
AMPLIMITE,ASY,RCPT,STD,90,ZN,4,CT



TE Part # 1757824-7
AMPLIMITE,ASY,RCPT,STD,90,ZN,1,CT



TE Part # 1757824-8
AMPLIMITE,ASY,RCPT,STD,90,ZN,2,
CONT



TE Part # 1757824-9
AMPLIMITE,ASY,RCPT,STD,90,ZN,3,CT



TE Part # 204512-2
RECEPT ASSY,SZ 1,AMPLIMITE



TE Part # 204518-2
RECEPT ASSY,62 POSN,AMPLIMITE




TE Part # 207684-4
AMPLIMITE,SKT CONT,SZ 22



TE Part # 1-1757824-1
AMPLIMITE,ASY,RCPT,STD,90,ZN,5,CT



TE Part # 211012-4
AMPLIMITE CONN SVR,44 POS,TRW



TE Part # 208866-1
PLUG ASSY,15 POSN,AMPLIMITE

Documents

Product Drawings

INSERTION/EXTRACTION TOOL



English

Instruction Sheets

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English