

91067-2 ✓ ACTIVE

TE Internal #: 91067-2

TE Internal Description: INSERTION/EXTRACTION TOOL

Mil-Spec: [M81969/1-02]

[View on TE.com >](#)



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 212561-2
CONN SAVER, SZ 3, AMPLIMITE



TE Part # 206801-2
AMPLIMITE RECEPT ASY, 25 POS



TE Part # 207253-2
RECEPT ASSY, 9 POSN, AMPLIMITE



TE Part # 206800-2
PLG ASSY, 25 POS, AMPLIMITE



TE Part # 207252-2
PLUG ASSY, SZ 1, AMPLIMITE



TE Part # 1-212565-0
AMPLIMITE, PIN CONT, SZ 20, AU PLTD



TE Part # 206802-1
PLUG ASSY, 37 POSN, AMPLIMITE



TE Part # 212560-2
CONN SAVER, 15 POSN, AMPLIMITE



TE Part # 212562-2
AMPLIMITE CONN SVR, 37 POS, TRW



TE Part # 2335889-3
AMPLIMITE SZ 3 PLUG, 25 POS, ST STL SHEL



TE Part # 2335889-4
AMPLIMITE SZ 4 PLUG, 37 POS, ST STL SHEL



TE Part # 211638-4
HD109 9 POS GMT ASY PLUG



TE Part # 448815-1
AMPLIMITE, ASY, PLUG, 109, NM, CS, 1



TE Part # 448816-2
AMPLIMITE, ASY, RCPT, 109, NM, CS, 2




TE Part # 211634-4
GMT ASY, RCPT 15 POSN, AMPLIMITE



TE Part # 448816-1
AMPLIMITE, ASY, RCPT, 109, NM, CS, 1



TE Part # 206803-1
AMPLIMITE RECEPT ASY, 37 POS,



TE Part # 1484949-1
AMPLIMITE RPT ASY, 37P, SZ4, SER109



TE Part # 206801-1
AMPLIMITE RECEPT ASY, 25 POS



TE Part # 211633-4
HD109 9 POS GMT ASY RCPT

Documents

[Product Drawings](#)

[INSERTION/EXTRACTION TOOL](#)



English

Instruction Sheets

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English