

Hawthorne

Outdoor Ceiling Mount 3000K

Fixture Type:
Catalog Number:
Project:
Location:

Model & Size	Color Temp & CRI	Finish	Watt	LED Lumens	Delivered Lumens
FM-W33113 11"	3000K 90	BK Black	20W	941	684

Example: FM-W33113-BK

For custom requests please contact customs@waclighting.com

FFATURES

- Hammered glass panels on five sides
- · Stainless steel textured reflector
- Driver concealed within the canopy
- 5 Year warranty

SPECIFICATIONS

Color Temp: 3000K

Input: 120/277 VAC,50/60Hz

CRI: 90

Dimming: ELV: 100-10% ,TRIAC: 100-10%

Rated Life: 50000 Hours

Mounting: Can be mounted on ceiling or wall in all orientations


Standards: ETL, cETL,IP65

Wet Location Listed

Construction: Aluminum body, hammered glass diffuser



RPL-GLA-33113-SI - Side Glass




FINISHES:



Black

LINE DRAWING:





FM-W33113