

Fixture Type: \_\_\_\_\_

Catalog Number: \_\_\_\_\_

Project: \_\_\_\_\_

Location: \_\_\_\_\_

## Sirius

Pendant 3000K

Model & Size	Color Temp & CRI	Watt	LED Lumens	Delivered Lumens	Finish
PD-81118 18"	3000K 90	35W	1523	466	AL Brushed Aluminum
		35W	2493	1218	BK Black

Example: **PD-81118-AL**

### DESCRIPTION

Full circle. A simple glowing halo completes.

### FEATURES

- Up and downlight with recessed silicone diffuser
- Low profile, adjustable powered aircraft cables for an ultra-clean look
- Quick spin-on canopy design with minimal hardware for easy installation
- Can be mounted on slope ceiling
- Driver concealed within the canopy
- 5 year warranty

### SPECIFICATIONS

Color Temp:	3000K
Input:	120 VAC, 50/60Hz
CRI:	90
Dimming:	ELV: 100-10%, TRIAC: 100-10%
Rated Life:	50000 Hours
Standards:	ETL, cETL, Title 24: 2019 Damp Location Listed
Construction:	Aluminum body, silicone diffuser

### REPLACEMENT PARTS


HDW-SY21-CE - Hardware Pack



### FINISHES



### LINE DRAWING



PD-81118

# WAC LIGHTING

Fixture Type: \_\_\_\_\_

Catalog Number: \_\_\_\_\_

Project: \_\_\_\_\_

Location: \_\_\_\_\_

## Sirius

Pendant 3000K

Model & Size	Color Temp & CRI	Watt	LED Lumens	Delivered Lumens	Finish
PD-81124 24"	3000K 90	49W 49W	2156 3480	623 1725	AL Brushed Aluminum BK Black

Example: **PD-81124-AL**

### DESCRIPTION

Full circle. A simple glowing halo completes.

### FEATURES

- Up and downlight with recessed silicone diffuser
- Low profile, adjustable powered aircraft cables for an ultra-clean look
- Quick spin-on canopy design with minimal hardware for easy installation
- Can be mounted on slope ceiling
- Driver concealed within the canopy
- 5 year warranty

### SPECIFICATIONS


Color Temp:	3000K
Input:	120 VAC, 50/60Hz
CRI:	90
Dimming:	ELV: 100-10%, TRIAC: 100-10%
Rated Life:	50000 Hours
Standards:	ETL, cETL, Title 24: 2019 Damp Location Listed
Construction:	Aluminum body, silicone diffuser

### REPLACEMENT PARTS


HDW-SY21-CE - Hardware Pack



### FINISHES



### LINE DRAWING



PD-81124